

NYS221**NYS Product Range / Jacks**

TECHNICAL DATA

Electrical

Rated Current: Depends on mating connector

Contact Resistance: Depends on mating connector

Insulation Resistance: > 1 G Ohm

Dielectric strength: 500 dc

Mechanical

Life Cycles: 5000

Cable OD: 4-9 mm

Solderability: IEC68-2-20

Operating Temperature: -25° C to +70° C

Material

Housing/Handle: Brass Ni/Au/black plated or Zinc Diecast

Insulation: Thermoplastic

Contacts: Brass Ni/Au plated

Strain Relief: CRIMP type SnCe plated

Copyright © 2005**Neutrik® AG.****All Rights Reserved.****NEUTRIK®**

CONNECTING THE WORLD

Neutrik® AG - Headquarters

Im alten Riet 143

9494 Schaan

Principality of Liechtenstein

phone: +423 2372424**fax:** +423 2325393**email:** neutrik@neutrik.com**net:** <http://www.neutrik.com>