Combination Pliers
Wire Strippers and Dismantling Tools
Gripping Pliers
Grip Pliers
Circlip Pliers
Carpenters' Pincers
Concreters´ Nippers
Cutting Pliers
Bolt Cutters
Bolt End Cutting Nippers
Concrete Mesh Cutter
Diagonal Cutter for fibre optics
Diagonal Cutters
Diagonal cutters for plastics
Electro-Mechanics' Diagonal Cutters
Electronic Super Knips®
Electronic Super Knips® ESD
Electronics Diagonal Cutters
Electronics Diagonal Cutters
Electronics Diagonal Cutters ESD
Electronics Diagonal Cutters with carbide cutting edges
Electronics Diagonal Cutters with carbide cutting edges ESD
Electronics End Cutting Nippers
Electronics End-Cutting Nippers ESD
Electronics Oblique Cutting Nipper
End Cutting Nipper
End Cutting Nippers for mechanics
High Leverage Diagonal Cutters
High Leverage End Cutting Nippers
High Leverage Flush Cutter
High-leverage centre cutters
KNIPEX CoBolt®
KNIPEX CoBolt® "Fencing"
KNIPEX CoBolt® XL
KNIPEX TwinForce®
KNIPEX X-Cut®
Precision Electronics Diagonal Cutters
Precision Electronics Diagonal Cutters ESD
Pipe Wrenches and Water Pump Pliers
Special Pliers and Tool Lamp
Precision Tweezers
Cable and Wire Rope Shears
Crimping Pliers
Crimp Assortments
Cable Connectors

74 02 160 High Leverage Diagonal Cutter



Technical details | Description | Special | Applications | Video

	No.	74 02 160
	Pliers	black atramentized
	Head	polished
	Handles	with multi-component grips
	Style	0
	medium hard wire	**9/64 Ø Inch** 3,4 Ø mm
	hard wire	**3/32 Ø Inch** 2,5 Ø mm
	piano wire	**5/64 Ø Inch** 2,0 Ø mm
	Length	**6 1/4 Inch** 160 mm
	Net weight	**0,461 lbs** 209 g

technical change and errors excepted

Downloaded from Arrow.com.

Insulated Tools
Tools with tethering
Control Cabinet Keys
Tool Kits
Tool Bags / Cases
Sales Aids
spare parts
Symbols
Orbis products
Rennsteig products

Downloaded from Arrow.com.