



Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFSta-Strap Ca ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'SST8H-L'

Your search criteria matched only one product, shown below

SST8H-L



- For indoor use
- Used for normal bundling and through -panel applications
- Small head height allows more efficient use of space in compact areas
- Exclusive two-piece design offers the lowest threading force in the industry
- Average 14% lighter than one -piece cable ties
- Releasable prior to final tensioning for bundle modifications
- Straight Tip design

	Part Number	SST8H-L
	RoHS Compliancy Status	Compliant
	Part Description	Cable Tie, Releasable, 27.5", LightHeavy cross section
	Product Type	Cable Ties
	Material	Nylon 6.6
	Color	Natural
	CSA Certified	Yes
	Mil. Std. Part Number	MS3367-6-9
	UL Listed (File #E56854)	No
	UL Recognized (File #E56854)	Yes
	Length (In.)	27.5
	Length (mm)	699
	Width (In.)	.300
	Width (mm)	7.6
	CE Compliant	Yes
	Cross Section	Light-Heavy
	Head Height (In.)	.325
	Head Height (mm)	8.3
	Head Width (In.)	.460
	Head Width (mm)	11.7
	Locking Style	Releasable
	Material Flammability Rating	UL 94V-2
	Max. Bundle Diameter (In.)	8.00
	Max. Bundle Diameter (mm)	203
	Max. Continuous Use Temperature	185°F (85°C)
	Min. Loop Tensile Strength (Lbs.)	120
	Min. Loop Tensile Strength (N)	534
	Pricing Description	Cable Tie, 2Piece, 27.5"L (699mm), LightHeavy, Nylon, Natural
	Thickness (In.)	.067
	Thickness (mm)	1.7
	Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
	Min. Order UOM	PC
	Min. Order Qty.	50
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.