Part Number : 151340606
Product Description : PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, 6 Circuits, Natural
Series Number : 15134
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

151340606_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	15134
Description	PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, 6 Circuits, Natural
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PicoBlade-to-PicoBlade
Product Name	PicoBlade
Type	Discrete Wire Assembly
UPC	889056871563

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Physical

Cable Length	600.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze

Downloaded from Arrow.com.

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	6.874/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Vertical, Single Row, Through Hole Headers	53047
PicoBlade Right-Angle, Single Row, Through Hole Headers	53048
PicoBlade Right-Angle, Single Row, Surface Mount Headers	53261
PicoBlade Vertical, Single Row, Surface Mount Headers	53398
PicoBlade Single Row Plug Housings	51047

Downloaded from Arrow.com.