



**Catalog No. C10-10**

**Description: NONINS RING TERM, 12-10, No10, META**

**UPC No 786210803463**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Non-Insulated Ring Terminal, Length .85 Inches, Width .38 Inches, Bolt Hole #10, Wire Range #12-#10 AWG, Copper, Tin Plated

**Descriptors**

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.

**Specifications**

Voltage Rating	600 V
Material	Copper
Color	Metallic

**Classifications**

Brand Name	Sta-Kon
Standard	UL E9809

**Dimensions**

Wire Size	12-10 AWG
-----------	-----------

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10



ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10

**Certification/Standard**

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A