




Part Number : 190720008
Product Description : VibraKrimp Ring Tongue
Terminal for 22-18 AWG Wire, Stud Size 4
(M2.6), Length 16.69mm
Series Number : 19072
Status : New Business Not Supported
Product Category : Ring and Spade Terminals
Engineering Number : AA-420-04



NO IMAGE AVAILABLE

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Ring and Spade Terminals
Series	19072
Description	VibraKrimp Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 4 (M2.6), Length 16.69mm
Keyword	Ring Terminal, Ring Terminals
Product Name	VibraKrimp
Type	Ring
UPC	800753073524

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.572/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	4 (M2.6)
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640016700</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640056700</u>

This document was generated on Mar 08, 2025