

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42984	04/19	GPF
A	DCN 48594	05/23	GPF

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

SMMP JACK (3221-40006)

SMA PLUG (SF2906-6002)

T-FLEX 405

M23053/5

SV P/N	OAL
7032-7526	6.000
7032-7527	12.000

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

50 OHMS

DC TO 18.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63. MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	 www.svmicrowave.com TITLE: SMPM JACK TO SMA PLUG FOR Ø.085 T-FLEX 405 CABLE ASSEMBLY SIZE B DWG. NO. 7032-7526-7527 SCALE: 2:1 SHEET 1 OF 1
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'		
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005		
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		
THIRD ANGLE PROJECTION		DRAWN: SJ 04/24/19	CHECKED: GPF 04/24/19	APPROVED: GPF 04/24/19

Downloaded from [Arrow.com](#)