

M12 transf. recpt. front mounting kit



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 301 2006
Specification	M12 transf. recpt. front mounting kit
HARTING eCatalogue	https://harting.com/21033012006

Identification

Category	Accessories
Series	Circular connectors M12
Identification	PushPull
Type of accessory	Housing
Description of the accessory	for front mounting

Version

Gender	Female
Locking type	Screw locking PushPull

Technical characteristics

Tightening torque	2 Nm Lock nut
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

Material (accessories)	Brass, nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	30
Net weight	18.419 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140236417
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400