

Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, White, 6-in. (15.24 cm)

MODEL NUMBER: **P137-06N-HDVW**



Mini DP to VGA/DVI/HDMI adapter connects your Mini DisplayPort or Thunderbolt 1/2 laptop or tablet to a VGA, DVI or HDMI display.

Features

Mini DP to VGA/DVI/HDMI Converter Connects Mini DisplayPort Laptop to a VGA, DVI or HDMI DisplayNo more carrying around separate adapters for various monitors, projectors and televisions. This Keyspan® Mini DP to VGA/DVI/HDMI adapter connects a VGA, DVI or HDMI display to the Mini DisplayPort or Thunderbolt 1 or 2 port on your Chromebook, MacBook, Microsoft Surface or other compatible laptop or tablet. Only one display may be connected at a time.

Simple All-in-One Solution for Displaying Video on a Large ScreenThe P137-06N-HDVW is ideal for classrooms, lecture halls and anywhere else you may give a video presentation away from the office. Just connect the converter between your laptop and whatever VGA, DVI or HDMI display device is on hand. You no longer have to dig around in your laptop bag for the correct adapter.

Transmits Outstanding 1080p Video for High-Definition PresentationsThis all-in-one unit features separate female HD15, DVI and HDMI ports. All three support computer video resolutions up to 1920 x 1200 (including 1080p) and HD video resolutions up to 1920 x 1080 (1080p), as well as 36-bit Deep Color (12 bits per channel).

Passive Adapter for Use with Dual-Mode DisplayPort SourcesThe P137-06N-HDVW is a passive adapter that requires the connected computer to support DisplayPort++ (DP++). This allows HDMI and DVI signals to be passed through. Check the documentation for your Mini DisplayPort source for compatibility.

Ready to Use Right from the Package, So You Can Plug and Play ImmediatelyThe plug-and-play Mini DP to HDMI adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1 or 2 port. With its small size and built-in cable, the P137-06N-HDVW is recommended for stowing in your laptop bag and carrying to school, the office or elsewhere.

3-Year WarrantyThe P137-06N-HDVW is backed by a 3-year warranty, ensuring reliability and performance.

Highlights

- Multiple video outputs connect to most displays—no more carrying multiple adapters
- Delivers high-definition picture quality at resolutions up to 1920 x 1200, including 1080p
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Passive adapter requires connected computer to have DP++ port for signal pass-through

Applications

- Connect your laptop to a DVI, VGA or HDMI monitor without digging around for the correct adapter
- Add a larger monitor to your laptop to use as a secondary display
- Giving video presentations in a classroom, lecture hall or conference room

System Requirements

- Source device with Mini DisplayPort, Thunderbolt 1 or Thunderbolt 2 output that supports DisplayPort++
- Display device with VGA, DVI or HDMI input
- VGA, DVI or HDMI cabling
- Not for use with MST hubs. For compatibility with MST hubs, use a DisplayPort 1.2-compliant product, such as P137-06N-HDV-4K.

Package Includes

- P137-06N-HDVW Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Converter Adapter, Thunderbolt 1/2, 1080p, White
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332210623
Product Type	Video Adapter
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
INPUT	
Product Length (in.)	6.00
PHYSICAL	
Color	White
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% TO 85% RH, Non-Condensing
Storage Humidity Range	5% TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty