



Cable Length L	Part Number					
	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable		Cat. 5e Outdoor UTP 4 Pair, AWG24 Solid Black Cable		Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	
	Metallized Plastic Plug Housing	Zinc Die-Cast Plug Housing	Metallized Plastic Plug Housing	Zinc Die-Cast Plug Housing	Metallized Plastic Plug Housing	Zinc Die-Cast Plug Housing
0,61m ± 0.01m			17-132884			
1m ± 0.01m	17-131684	17-131724	17-131804	17-131854	17-131934	17-131984
2m ± 0.02m	17-100964	17-131734	17-101024	17-131864	17-101054	17-131994
3m ± 0.03m	17-131694	17-131744	17-131814	17-131874	17-131944	17-132004
4m ± 0.04m	17-100974	17-131754	17-101034	17-131884	17-101064	17-132014
5m ± 0.05m	17-100984	17-131764	17-101044	17-131894	17-101074	17-132024
10m ± 0.10m	17-131704	17-131774	17-131824	17-131904	17-131954	17-132034
15m ± 0.15m	17-131714	17-131784	17-131834	17-131914	17-131964	17-132044
20m ± 0.20m	17-102864	17-131794	17-131844	17-131924	17-131974	17-132054

Notes: Special cable length up to 20 meters are available please contact factory; UPT: Unshielded Twisted Pair, STP: Shielded Twisted Pair

Notes:

- Electrical:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Connector Operating Temperature: - 40 °C to + 85 °C
- Materials and Finish:
 - Metal Coupling Ring: Brass, Nickel Plated
 - Plug Housing: Metallized ABS (UL94 V-0) or Zinc Die-Cast, Nickel Plated
 - Interfacial Seal: Silicone, Color: White
 - Cable Gland: Brass, Nickel Plated
 - Cable Gland Seal: NBR, Color: Black
 - Cat.5e RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - Cat.5e RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
 - Cat.5e RJ45 Plug Contacts: Phosphor Bronze, Finish: 50 µm Gold min. over Nickel
 - RJ45 Modular Boot: PVC, Color: Black
 - Cable: See Part Number Table

Index: e 11.06.2025 JLE		Scale/ Maßstab: 1,2:1	dim. in mm		RJ45 Cat. 5e Ethernet Patch Cord, IP67 Industrial to Standard, M28 Thread screw type (Metal version) <i>RJ45 Cat. 5e Ethernet-Patchkabel, IP67 Industriestandard, M28 Schraubgewinde (Metallversion)</i>		dwg no / Z.-nr.: 17K1A112	DIN-A3 1 / 1
			Date/Datum	Name				
drawn/gez.	12.12.2008	Vincent Ke	appd./gepr.	12.12.2008				



The reproduction, distribution and sale of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. We reserve the right to withdraw from circulation and/or to destroy copies of printed publications and files on data carriers at any time without notice. Inquiries should be directed to our Customer Service Department. © 2025 Amphenol Corporation. All rights reserved.