


RoHS
Compliant

VERSION	DESCRIPTION	DATE
1.0	New Release	2018/3/30



PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
911M-2-3-00100-PL	671-452-A	1000±100	Aqua
911M-2-3-00200-PL	671-452-B	2000±100	Aqua
911M-2-3-00300-PL	671-452-C	3000±100	Aqua
911M-2-3-00500-PL	671-452-D	5000±100	Aqua
911M-2-3-00700-PL	671-452-E	7000±100	Aqua
911M-2-3-01000-PL	671-452-F	10000±100	Aqua
911M-2-3-01500-PL	671-452-G	15000±100	Aqua
911M-2-3-02000-PL	671-452-H	20000±100	Aqua
911M-2-3-02500-PL	671-452-I	25000±100	Aqua

NOTES:

Insertion loss < 0.3 dB

CnC Tech, LLC
Industrial Cable and Connector Technology

6	
5	
4	Dust Cover
3	Shrinkage Tube
2	LC MM Duplex Connector (Beige housing White boot)
1	2.0mm,Duplex,MM-50/125 OM3, OFNP, Optical Fiber Cable(Aqua)
No.	Description

		TITLE		Patch Cord, LC-LC,MM-50/125 OM3, Duplex, OFNP, aqua, 2.0mm, xxm	
UNIT		P/N		above	DRAWN BY
unless otherwise stated Tolerances mm angular XXX.XX ±0.3 ±2° XX.XX ±0.2 X.XX ±0.1		Customer P/N		911M-2-3-0XXXX-PL	CHECK BY
SIZE A4		SCALE Free		PAGE	1/1
				APPROVAL BY	