


	1	2	3	4	5	6	7

USB AM TYPE MALE

P1

1800±30mm

P2



NOTES:

1.CABLE: UL 2725 28AWG*1P+28AWG*2C+AL/MY+B OD=3.8±0.2mm JACKET COLOR: BEIGE

CABLE MUST PRINT: E***UL***** AWM STYLE 2725 80°C 30V VW-1

2.CONNECTOR:

P1: USB A/M, GOLD PLATED CONTACTS, NICKEL PLATED SHELL

P2 :USB B/M, GOLD PLATED CONTACTS, NICKEL PLATED SHELL

3.HOOD: MOLDED TYPE,PVC 45P,COLOR:BEIGE



4.ELECTRICLE TEST:

(1)100% OPEN SHORT & MIS WIRE TEST.

(2)CONTACT RESISTANCE 3 ohm Max .

(3)INSULATION RESISTANCE 10M ohm Min .

(4)HI-PDT TEST:DC 300V/10ms



ASSMANN WSW P/N	LENGTH
AK-300105-010-E	1.0 M
AK-300105-018-E	1.8 M
AK-300105-030-E	3.0 M

D

D

G

G

RoHS compliant

Scale	FREE						
TOLERANCE							
X.	±X						
X.X	±X						
X.XX	±X						
DIM	TOL						
X.°	±X°						
X.X°	±X°						
Angle	TOL	Id.	Modification	Date	Name		

ASSMANN
WSW/ components

Customer-No.					
	Drawn	06.07.2009	Rale		
	Approved	06.07.2009	Meng		
ASSMANN WSW-No.					
AK-300105-xxx-E					
Drawing-No.					
ASS 3635 CA					
Replace					
rev02					
Sheet					

H

H

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--