



Representative Image

Catalog No. F2036

Description: INS PP FERRULE 14, 2.5 MM2, LG .74

UPC No 786210335162

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Polypropylene-Insulated Ferrule, Total Length .748 Inches/19mm, Pin Length .472 Inches/12mm, Pin Diameter .091 Inches/2.3mm, Base Diameter .165 Inches/4.2mm, Wire Range 14 AWG/2.50mm², Color Blue, Copper, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.

Specifications

Material	Copper
Color	Blue

Classifications

Brand Name	Sta-Kon
Standard	UL E489056 UL E489056

Dimensions

Wire Size	14 AWG
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	2.5 mm ²
Insulated	Y
Material insulation	Polypropylene
Colour	Blue
Material	Copper

by ABB

ETIM	EC000005 Cable end sleeve
Surface protection	Tinned
With identification flag	N
Reel packaging	N
AWG size	14