
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

creo
Creo Parametric 3.0
DO NOT REVISE EXCEPT BY CAD

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REDRAW BY CAD ECO-16-012742	01FEB2017	NCL	DAO



1 - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2 - DIMENSÕES NÃO ENCONTRADAS DEVEM SER OBTIDAS DO CAD 3D DA PEÇA,DEVENDO-SE EMPREGAR O VALOR DA TOLERÂNCIA LINEAR COM UMA CASA DECIMAL,MOSTRADO NA TABELA DE TOLERÂNCIA GERAL NESTE DESENHO.

2 - NOT FOUND DIMENSIONS MUST BE GOTTEN FROM THE PART 3D CAD DATABASE AND MUST BE USED THE VALUE OF THE LINEAR TOLERANCE WITH ONE DECIMAL PLACE, SHOWN IN THE TOLERANCE TABLE ON THIS DRAWING.

OBSOLETE (1)

VW PART NUMBER	REQ.PER ASSY -8	-7	-6	-5	-4	-3	-2	-1	ITEM	DESCRIPTION	MATERIAL	FINISH
813 971 958 - G								1	1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	CINZA/GRAY
813 971 958 - F							1		1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	VERDE/GREEN
813 971 958 - E						1			1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	BRANCO/WHITE
813 971 958 - D					1				1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	AZUL/BLUE
813 971 958 - C				1					1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	AMARELO/YELLOW
813 971 958 - B			1						1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	VERMELHO/RED
813 971 958 - A		1							1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	MARROM/BROWN
813 971 958	1								1	4 WAY .250 FASTIN-ON TAB HSG	PA 6.6	PRETO/BLACK
	881208								2	O´RING	NEOPRENE/NITRILICA	PRETO/BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0,3
2 PLC ±0,2
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL SEE TABLE -
FINISH - -

DWN NCLAPRESA 31JAN2017
CHK FFORTUNATO 31JAN2017
APVD DAOLIVEIRA 31JAN2017
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME 4 WAY 250 FASTIN-ON TAB HSG ASSY
- -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-881208	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV A3

1470-19 (3/13)

Downloaded from Arrow.com.