


D-SUB STANDARD

Solder pin – Angled – .318" / 7.19 mm – Stamped contacts – Plastic bracket




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

SOCKET CONNECTOR





No. of pos.	A -0.76	B -0.25	C
09	31.19	16.46	25.00 ± 0.12
15	39.52	24.79	33.30 ± 0.15 ± 0.10
25	53.42	38.50	47.04 ± 0.13
37	69.70	54.96	63.50 ± 0.13

Mounting style: PCB clip, threaded insert




Mounting style: PCB clip, front spacer



DESCRIPTION


- Mounting styles:
 - with mounting bracket, PCB clip and 4-40 UNC threaded insert
 - with mounting bracket, PCB clip and 4-40 UNC hex bolt
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated

PLUG CONNECTOR





No. of pos.	A -0.76	B -0.25	C	D -0.3
09	31.19	16.79	25.00 ± 0.12	6.12
15	39.52	25.12	33.30 ± 0.15 ± 0.10	6.12
25	53.42	38.84	47.04 ± 0.13	5.99
37	69.70	55.30	63.50 ± 0.13	5.99

Mounting style: PCB clip, threaded insert



Mounting style: PCB clip, front spacer



ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	PCB clip/Threaded insert	302 A 11339 X
15	PCB clip/Threaded insert	302 A 11349 X
25	PCB clip/Threaded insert	302 A 11359 X
37	PCB clip/Threaded insert	302 A 11369 X
09	PCB clip/Hex bolt	302 A 11249 X
15	PCB clip/Hex bolt	302 A 11259 X
25	PCB clip/Hex bolt	302 A 11269 X
37	PCB clip/Hex bolt	302 A 11279 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	PCB clip/Threaded insert	301 A 11029 X
15	PCB clip/Threaded insert	301 A 11039 X
25	PCB clip/Threaded insert	301 A 11049 X
37	PCB clip/Threaded insert	301 A 11059 X
09	PCB clip/Front spacer	301 A 10939 X
15	PCB clip/Front spacer	301 A 10949 X
25	PCB clip/Front spacer	301 A 10959 X
37	PCB clip/Front spacer	301 A 10969 X

PCB clip .122" / 3.1 ± .004" / 0.10 mm hole diameter and .063" / 1.6 mm circuit board thickness