


Honeywell Sensing and Control

Search



2TL1-56K

(Home : Products : Switches > MICRO SWITCH™ Toggle Switches > TL)

Actual product
appearance
may vary.

TL Series Toggle Switch, 2 pole, 3 position, Screw terminal, Locking Lever, Military Part Number MS27408-2K

[Sales & Service](#)[Distributor Inventory](#)**narrow your search****Products**

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6004)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (988)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1409)
- More...

new products**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Circuitry/Operating action

Product Type

MICRO SWITCH™ Toggle Switch

Looked in center and extreme position (Opposite keyway)

Ampere/Voltage Range (Resistive Load)

0.75 A at 115 Vdc, 0.5 A at 250 Vdc, 0.5 A to 10 A at 0.5 Vac to 277 Vac, 0.5 A to 18 A at 0.5 Vdc to 28 Vdc

Circuitry

DPDT

Action

3 position

Mounting

Bushing 15/32 in

Termination

Screw

MIL Spec. Number

MS27408-2K

Lever Type

Locking

UL/CSA

L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"

Comment

Silver cadmium oxide contacts

Availability

Global

UNSPSC Code

30211908

UNSPSC Commodity

30211908 Toggle switches

Series Name

TL

contacts

- ▷ Customer Service
- ▷ Technical Support
- ▷ Global Sales & Service
- ▷ View Site Demo
- ▷ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▷

Meet Dr. Larry

**my links**

- ▷ Login to iCOM
- ▷ Login to Rep/AD Portal
- ▷ Login to Digital University

News Center

▷ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

▷ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

▷ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

▷ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

▷ HONEYWELL INTRODUCES MICROPower OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH
Anniversary site

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)