


Part Number : 1201010002
Product Description : PROFIBUS Data Line Micro-Change (M12) Tee, 5 Poles, Male/Female with Male Drop
Series Number : 120101
Status : Obsolete
Product Category : Industrial Tees and Splitters
Engineering Part Number : PDTS01

Documents and Resources

Drawings

1201010002_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Tees and Splitters
Series	120101
Description	PROFIBUS Data Line Micro-Change (M12) Tee, 5 Poles, Male/ Female with Male Drop
IP Rating	IP67
Product Name	PROFIBUS Data Line
Type	Drop Tee
UPC	78678853913

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC/DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Length	0.066m
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	1548.130/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female

Obsolete

Downloaded from Arrow.com.

Temperature Range - Operating	-20° to +80°C

Obsolete

Downloaded from Arrow.com.