

Product information

BAT-ANT-N-18A-V-IP65

Industrial Ethernet:Industrial Wireless LAN:Wireless Accessories :Wireless LAN Antennas:BAT-ANT-N-18A-V-IP65

<https://catalog.beldensolutions.com:443/link/57078-24455-49859-24498-24499-64478/en/conf/ui.state>

Name	BAT-ANT-N-18A-V-IP65
	Directional antenna for 5 GHz band.
Delivery informations	
Availability	available
Product description	
Description	Directional antenna for 5 GHz band.
Type	BAT-ANT-N-18A-V-IP65
Order No.	943 981-006
Cable length	1 m
Cable specification	N-plug to N-plug
Radio technology	
Frequency band	5150 - 5850 MHz
Polarisation	linear, vertical
Elevation, Azimuth	18° / 18°
VSWR	1.5
Gain	18 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-45 °C to +70 °C
Storage/transport temperature	-45 °C to +70 °C
Wind load	104 N at 220 km/h
Mechanical construction	
Dimensions (W x H x D)	190 x 190 x 30.5 mm
Mounting	wall, mast
Protection class	IP65
Material	ASA
Weight	0.7 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 1 m cable, pigtail, mounting material

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.