





-Protection level: IP67/65
-Temperature range: -40°C ...+70°C


X
without protection cap



Loading-Plan

A — blue — B
B — orange — A

Y
without protection cap



9	Fiber optic cable breakout Multi Mode	33 58 211 300 0004	300 ± 3 m
8	Fiber optic cable breakout Multi Mode	33 58 211 100 0004	100 ± 1 m
7	Fiber optic cable breakout Multi Mode	33 58 211 060 0004	60 ± 0,6 m
6	Fiber optic cable breakout Multi Mode	33 58 211 050 0004	50 ± 0,5 m
5	Fiber optic cable breakout Multi Mode	33 58 211 040 0004	40 ± 0,4 m
4	Fiber optic cable breakout Multi Mode	33 58 211 020 0004	20 ± 0,2 m
3	Fiber optic cable breakout Multi Mode	33 58 211 010 0004	10 ± 0,1 m
2	Fiber optic cable breakout Multi Mode	33 58 211 005 0004	5 ± 0,05 m
1	Fiber optic cable breakout Multi Mode	33 58 211 001 0004	1 ± 0,015 m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maßel/Free size tolerances				
For Information Only not to be replaced when changed				Dat.	Name	Maßstab/Scale /	FO cable assembly 2xPush Pull LC duplex Multimode 50 µm			
			Detail.	16.11.09	MS					
			Insp.	16.11.09	RA					
			Stand.							
DRS761A	07.07.10	MS	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 33 58 211 xxx 0004			Blatt/
DRS539B										
Mod.	Dat.	Name				Sub.				