



Part Number : [1300940241](#)

Product Description : Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 762.04kg (1680 lbs), Stainless Steel

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Part Number : 35035SS



Documents and Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:68907546-fa8c-4b3d-9e3f-c4db413c3bda
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 762.04kg (1680 lbs), Stainless Steel
NEMA Rating	NEMA 4
Product Name	Standard Duty
Type	Support Grip
UPC	78678809774

Physical

Approximate Break Strength	762.04kg (1680 lbs)
Bale Length	0.305m (12.00")
Body Style	Straight
Cable Diameter	38.10-44.20mm (1.500-1.740")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Stainless Steel
Mesh Length	0.432m (17.00")
Net Weight	587.000/g
Number of Holes	N/A

O-Ring	No
Thread Size	N/A

This document was generated on Dec 18, 2025