


Specification Sheet

Part Number: CTAM110M4

Suitable for applications with minimal space.

CTAM has 4-way entry design for use in line or at 90° angle to cable run.

CTAM mounts are available in different sizes and materials.



Cable Tie Anchor Mount, 0.17" Hole Dia, 0.20" Max Tie Width, PA66, White, 1000/pkg

Article Number	151-31106
Type	CTAM1
Color	White (WH)
Quantity Per	pack
Product Description	Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.
Short Description	Cable Tie Anchor Mount, 0.17" Hole Dia, 0.20" Max Tie Width, PA66, White, 1000/pkg
Global Part Name	CTAM1-PA66-WH

Length L (Imperial)	0.8
Length L (Metric)	20.4
Fixation Method	Screw Mount
Width W (Imperial)	0.4
Width W (Metric)	10.2
Cable Ties	T18 - T50
Height H (Imperial)	.20
Height H (Metric)	5.10
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.3 mm
Mounting Hole Diameter D Max (Metric)	4.3
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)