



har-port USB coupler

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Compact and robust design
- Practical accessories

Technical characteristics

Number of ports	2x USB Typ A
Mounting	Screwable in cover plates
Degree of protection	IP20
Mating cycles	min. 1500
Temperature range	-25 °C ... +70 °C
Housing material	Polyamide

Identification	Part No.	Drawing	Dimensions in mm
<i>har-port</i> USB 2.0 A-A coupler	09 45 452 1901		
<i>har-port</i> USB 3.0 A-A coupler	09 45 452 1902		
<i>har-port</i> USB 2.0 A-A coupler with cable			
Length: 0.15 m	09 45 452 1927		
0.4 m	09 45 452 1928		
0.5 m	09 45 452 1920		
1.0 m	09 45 452 1921		
1.5 m	09 45 452 1922		
2.0 m	09 45 452 1923		
3.0 m	09 45 452 1924		
4.0 m	09 45 452 1926		
5.0 m	09 45 452 1925		
<i>har-port</i> USB 2.0 B-B coupler with cable			
Length: 0.5 m	09 45 452 1910		
1.0 m	09 45 452 1911		
1.5 m	09 45 452 1912		
2.0 m	09 45 452 1913		
3.0 m	09 45 452 1914		
4.0 m	09 45 452 1916		
5.0 m	09 45 452 1915		