Datasheet for part number DBMZ-25S-N-K126

Our Catalog Part Number: DBMZ-25S-N-K126
Our Global Manufacturing Part Number: 053513-2279
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	200
Contact Arrangement	25 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	Steel
Shell Finish	Pure tin over nickel
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contact Type	Straight PCB
Contact Material	copper alloy
Contact Finish	30 microinch gold over 50 microinch nickel
Hardware	.300" (7.6mm) 4-40 Standoff, Boardlock

Specifications and dimensions subject to change.

Downloaded from Arrow.com.