




D



SECT "G"—"G"



9P ONLY



SECT "H"—"H"





Fig-1

1. PEELING RESISTANCE: 0.196N(20gf)–0.686N(70gf)  
SPEED: 300mm/min

TOLERANCE UNLESS  
OTHERWISE SPECIFIED

|          |       |
|----------|-------|
| 10»*     | ±0.2  |
| 30»*»10  | ±0.25 |
| 100»*»30 | ±0.3  |
| ANGLE    | ±3°   |

|                                                                                       |  |                               |  |                                                                                                            |           |            |               |
|---------------------------------------------------------------------------------------|--|-------------------------------|--|------------------------------------------------------------------------------------------------------------|-----------|------------|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>JACH HOU<br>19SEP10    |  |  TE Connectivity Ltd. |           |            |               |
| DIMENSIONS:<br>mm                                                                     |  | CHK<br>MARTIN LI<br>19SEP10   |  |                                                                                                            |           |            |               |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                |  | APVD<br>STEVEN YAO<br>19SEP10 |  | NAME<br><br>EMBOSS<br>CT HEADER ASSY<br>BOX V SMT                                                          |           |            |               |
|  |  | PRODUCT SPEC<br>108-60016     |  |                                                                                                            |           |            |               |
| 0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±                       |  | APPLICATION SPEC              |  |                                                                                                            |           |            |               |
| MATERIAL                                                                              |  | FINISH                        |  | SIZE                                                                                                       | CAGE CODE | DRAWING NO | RESTRICTED TO |
|                                                                                       |  |                               |  | A3                                                                                                         | 00779     | C-292175   | —             |
| CUSTOMER DRAWING                                                                      |  |                               |  | SCALE                                                                                                      | N/A       | SHEET      | REV           |
|                                                                                       |  |                               |  |                                                                                                            |           | 1 OF 3     | R4            |



