



Pushing Performance
Since 1945

Han-Eco 6B-Cover-for SL-w. cord-HCC



| | |
|---------------|-------------------------------------|
| Part number | 19 43 006 5446 |
| Specification | Han-Eco 6B-Cover-for SL-w. cord-HCC |

Identification

| | |
|------------------------------|---|
| Category | Accessories |
| Series of hoods/housings | Han-Eco® B |
| Type of accessory | Protection cover |
| Description of the accessory | for bulkhead mounted housings for surface mounted housings for cable to cable housing With fixing cord |

Version

| | |
|--------------|----------------------|
| Size | 6 B |
| Locking type | Single locking lever |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |

Material properties

| | |
|---|--|
| Material (hood/housing) | Polyamide (PA) Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |



Pushing Performance
Since 1945

Material properties

| | |
|-------------------------------------|----------------------|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) |
| | R23 (HL 1-3) |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 61984 |
| | EN 45545-2 Fire protection on railway vehicles |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140829824 |
| ETIM | EC002314 |
| eCl@ss | 27440208 Cap for industrial connectors |