
HellermannTyton

Technical data sheet

Article number:
126-01004 **T50RSF(U)**



Product Group	1-Piece Fixing Ties with Arrowhead
Product Family	without wings and disc, for round holes
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)

Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Diameter max (metric)	44.5 mm
Bundle Ø min.	1.6 mm
CE Certification	Yes
Fixation Method	arrowhead
Flammability	UL 94 V2
for Hole Ø (FH)	6.4 - 7.1 mm
Height (H)	7.50 mm
Length (L)	210.82 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +125 °C
Panel Thickness	3.56 mm
Panel Thickness max.	1.0 - 3.56 mm
Panel Thickness min. (metric)	1.0 mm
ROHS compliant	Yes
Specifications	UL-ZODZ2.E64139
Thickness (T)	1.2 mm
UL-File Number	E64139
Variant	Inside Serrated
Width (W)	4.7 mm

RoHS

c UL us

created on 8. August 2024, 9:15 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.