


1735482-2 Product Details

[Share](#) | [Print](#) | [Email](#)


1735482-2

TE Internal Number: 1735482-2
Active

[View 3D PDF](#)

0.8mm Free Height

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector Style = Receptacle
- 60 Positions
- PCB Mounting Orientation = Vertical
- Board-to-Board Stack Height = 17.00 mm, 18.00 mm, 19.00 mm, 20.00 mm
- Gold (8) Contact Plating, Mating Area, Material

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ View Mating Products (17)
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Feedback](#)
[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- RECEPTACLE 17MM HEIGHT FH 0.8MM B-T-B CONNECTOR WITH... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- Free Height 0.8 mm Pitch Board-to-Board Connector (SMT) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version A)
- 3D Model (IGES, Version A)
- 3D Model (STEP, Version A)

[List all Documents](#)

Additional Product Images:

- Product Photo

Related Products:

- Tooling
- Mating Products (17)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- PCB Mounting Orientation = Vertical
- Family Name = Free Height
- Keyed = Yes
- Sealant = Without
- Cover Material = Steel

Dimensions:

- Board-to-Board Stack Height (mm [in]) = 17.00 [0.669], 18.00 [0.709], 19.00 [0.748], 20.00 [0.787]
- Height = 17H

Body Features:

- Locating Post(s) = With
- Vacuum Cover = With
- Locating Post Length = 0.5 mm

Contact Features:

- Contact Plating, Mating Area, Material = Gold (8)
- Contact Base Material = Copper Alloy
- Solder Tail Contact Plating = Tin over Nickel

Housing Features:

- Connector Style = Receptacle
- Housing Color = Natural
- Housing Material = LCP - GF (Liquid Crystal Polymer)
- Housing Material Temperature = High

Configuration Features:

- Number of Positions = 60
- Number of Rows = Dual

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- UL Flammability Rating = UL 94V-0

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

