
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

**1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568A. (I B)
4. CONSTRUCTED WITH 24AWG STRANDED CAT5e UTP CM PATCH CABLE
5. MATERIALS:
PLUG: POLYCARBONATE
6. NOMINAL CABLE DIAMETER IS 0.215 IN (5.46MM). (J)

(I F) T568A WIRING SCHEME

PLUG POSITION	CABLE WIRE
1	WHITE GREEN
2	GREEN
3	WHITE ORANGE
4	BLUE
5	WHITE BLUE
6	ORANGE
7	WHITE BROWN
8	BROWN

(C)

CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
ORANGE	OR
VIOLET	VL
(H) GRAY	GY

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
3	5-13-10	BJN		M. ADDED IDENTIFICATION LABEL L. ADDED TANGLE-FREE LATCH J. ADDED NEW NOTE 6 K. ADDED () TO P/N	02479-282			
2	7-25-07	BJN	EJH	I. T568A WAS T568B H. ADDED GY-GRAY	02479-282	REGA		
1	4-18-07	BJN	EJH	G. TX5e UTP WAS CATEGORY 5E W/PANDUIT PLUGS F. ADDED T568B WIRING SCHEME E. MODULAR PLUG WAS PANDUIT PLUG C. ADDED COLOR TABLE D. ADDED CABLE LG A. ADDED SH2 B. ADDED NOTES 3-5	02479-282	REGA		
R	3-21-06	NER	WJC	RELEASED TO PRODUCTION	02479-282	RMD		

SIZE A

DRAWING FILENAME: M02479KU_DC282/00D

TX5e UTP COPPER PATCH CORDS (CM) CUSTOMER DRAWING

(G)

PANDUIT® CORP.
TINLEY PARK, IL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± .06(1.5) (.XXX) ± .010(.3)
(.XX)± ANGLES ±

DRAWN BY: NER
DATE: 3-16-06
CHK'D: WJC
REVIEW DRAWING NUMBERS:

I.I. NUMBER:
PRODUCT SPEC:
WORK INSTRUCTION:
SCALE: NONE
PART NO.: UTPCHXX**(Y) (K)
DRAWING NO.: 02479-282
SHEET 1 OR 2

Downloaded from Arrow.com.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX5e UTP PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTPCH1**Y	1 FT.
UTPCH2**Y	2 FT.
UTPCH3**Y	3 FT.
UTPCH4**Y	4 FT.
UTPCH5**Y	5 FT.
UTPCH6**Y	6 FT.
UTPCH7**Y	7 FT.
UTPCH8**Y	8 FT.
UTPCH9**Y	9 FT.
UTPCH10**Y	10 FT.
UTPCH11**Y	11 FT.
UTPCH12**Y	12 FT.
UTPCH13**Y	13 FT.
UTPCH14**Y	14 FT.
UTPCH15**Y	15 FT.
UTPCH16**Y	16 FT.
UTPCH17**Y	17 FT.
UTPCH18**Y	18 FT.
UTPCH19**Y	19 FT.
UTPCH20**Y	20 FT.
UTPCH25**Y	25 FT.
UTPCH30**Y	30 FT.
UTPCH35**Y	35 FT.
UTPCH40**Y	40 FT.

PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTPCH0.5M**Y	0.5 m
UTPCH1M**Y	1 m
UTPCH1.5M**Y	1.5 m
UTPCH2M**Y	2 m
UTPCH2.5M**Y	2.5 m
UTPCH3M**Y	3 m
UTPCH4M**Y	4 m
UTPCH5M**Y	5 m
UTPCH6M**Y	6 m
UTPCH7M**Y	7 m
UTPCH8M**Y	8 m
UTPCH9M**Y	9 m
UTPCH10M**Y	10 m
UTPCH15M**Y	15 m
UTPCH20M**Y	20 m
UTPCH25M**Y	25 m
UTPCH30M**Y	30 m
UTPCH35M**Y	35 m
UTPCH40M**Y	40 m

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
3	5-13-10	BJN		SEE SHEET 1 FOR REVISIONS	02479-282			

DRAWING FILENAME: M02479KU_DC282/00D

SIZE: A

TX5e UTP COPPER PATCH CORDS (CM) CUSTOMER DRAWING

PANDUIT CORP. TINLEY PARK, IL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± .06(1.5) (.XXX) ± .010(.3)
(.XX)± ANGLES ±

DRAWN BY: NER
DATE: 3-16-06
CHK'D: WJC
REVIEW DRAWING NUMBERS

I.I. NUMBER:
PRODUCT SPEC:
WORK INSTRUCTION:
SCALE: NONE
PART NO.: UTPCHXX**(Y)
DRAWING NO.: 02479-282
SHEET 2 04 2

Downloaded from Arrow.com.