
TXR40AZ00-1008BI Product Details



Active

View 3D PDF

Braid, Fixed, Spin and Tinel Lock Adapters

TXR40AZ00-1008BI

TXR40AZ00-1008BI

TE Internal Number: CW4641-000

Product Highlights View All

- Applies To Cable
- Military Style Number = MIL-DTL-38999
- Style = Tinel Lock
- Connector Code = 40
- Straight

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

[+] Feedback

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Style	Tinel Lock
Angle	Straight
Connector Shell Size	10
Finish	Zinc Nickel
Color	Black

Dimensions

Boot Diameter (mm [in])	20.32 [0.800]
Cable Diameter Range (mm [in])	8.00 – 11.90 [0.320 – 0.470]

Body Features

Connector Code	40
Entry Size	8
Material	Aluminum Alloy

Configuration Features

Braid	Double 36 AWG Braid

Industry Standards

Government/Industry Qualification	No
Military Style Number	MIL-DTL-38999
RoHS/ELV Compliance	Not ELV/RoHS compliant
Lead Free Solder Processes	Not relevant for lead free process

Conditions for Usage

Applies To	Cable

Other

Brand	Raychem
Comment	For specific shell size information, refer to "Harnware" or Catalog.

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.