

## Power Extension Cord, C19 to Left Angle C20 - Heavy Duty, 20A, 250V, 12 AWG, 2 ft., Black

MODEL NUMBER: P036-002-20LA



Heavy-duty extension cable with left-angle C20 end allows connection of C19/C20 high-output devices in tight spaces or awkward angles.

### Features

**20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

**Left-Angle C20 Plug Makes Connecting in Tight Spaces Easier** The C19 to C20 left-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the left-angled C20 plug guides the heavy-duty extension cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

### Highlights

- Left-angle C20 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering servers, routers and other high-output network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 2 ft. away in your data center
- Extend an existing power connection up to 2 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

### Package Includes

- P036-002-20LA C19 to Left-Angle C20 Heavy-Duty Extension Cord, 2 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332156525
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	100-250
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
Power Cord Jacket Type	SJT
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	2
Cable Length (m)	0.6
Shipping Dimensions (hwd / cm)	0.64 x 13.21 x 22.10
Shipping Dimensions (hwd / in.)	0.25 x 5.20 x 8.70
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C20 - LEFT ANGLE
Side B - Connector 1	IEC-320-C19
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>