



Part Number : 1301020256

Series Number : 130102

Product Category : Lamps and Lights

Product Description : Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Side Outlet

Status : Active

Engineering Number : 271U

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102

Description	Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Side Outlet
NEMA Configuration	N/A
Product Family	Hand Lamps
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678860132

Agency

CSA	LR85374
UL	E59251

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Commercial
Guard Included	Yes
Guard Type	Reflector, Screw Release
Height	381.00mm (15.000")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

This document was generated on May 04, 2024