

WQB A/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, black, 24 A, Number of poles: 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 15.28 mm
Order No.	1578960000
Type	WQB A/3
GTIN (EAN)	4008190108960
Qty.	50 pc(s).

Creation date May 5, 2025 12:44:18 PM CEST

Catalogue status 26.04.2025 / We reserve the right to make technical changes.

WQB A/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.098 inch
Height	23.5 mm	Height (inches)	0.925 inch
Width	15.28 mm	Width (inches)	0.602 inch
Net weight	0.86 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., max.	70 °C		

Material data

Material	tinned copper	Colour	black
----------	---------------	--------	-------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	3	Rated current, multi-pole	24 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

General

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	3
---------------------	---	-----------------	---

Rating data

Rated voltage	800 V	Rated current	24 A
---------------	-------	---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

WQB A/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
------------------------	-----------------------------

REACH SVHC	No SVHC above 0.1 wt%
------------	-----------------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
------------------	---------------------------------

User Documentation	StorageConditionsTerminalBlocks
--------------------	---

Catalogues	Catalogues in PDF-format
------------	--