Part Number : 1301420037
Product Description : Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V
Series Number : 130142
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 2875



Documents and Resources

Drawings

1301420037_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Phosphine oxide, diphenyl(2,4,6-trimethylbenzoyl) per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130142
Description	Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V
IP Rating	N/A
NEMA Configuration	NEMA L15-30
Product Name	Super-Safeway
Specialty	N/A
Type	Plug
UPC	78678870433

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 250V

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Downloaded from Arrow.com.

Net Weight	210.660/g
Poles	3-pole/4-wire
Receptacle Type	N/A

Downloaded from Arrow.com.