

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008500109

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK Crimp Terminal, Series 2477, Humpback, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-08-50-001 (PDF)

Packaging Specification PK-2759-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	2477
Application	Power
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Product Name	KK
UPC	800753834248
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.162/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.54-2.79mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	4.25A, 5.0A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	2477-(P909)
Reference - Drawing Numbers	
Packaging Specification	PK-2759-002-001
Product Specification	PS-08-50-001
Sales Drawing	SD-2477-XXXX-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2477 Series

Mates With

2139 Crimp Housing

Use With

41696 Crimp Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Terminator Die	11402096
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 18-24 AWG	638279500
Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals,	638885000

18-24 AWG, check
ATS for Wire
Insulation Diameter
Compatibility

This document was generated on 02/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION