











PCB layout, component side



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302.

0955 155 6612 333		2	4-40 UNC	Black insulator	Samples	
0955 155 3612 741		1			Reel packaging (140 connectors)	
0955 155 6612 741		2				
0955 155 7612 741		3				
0955 155 3611 741		1	M3			
0955 155 6611 741		2				
0955 155 7611 741		3				
Part number		PL	Nut	Index designation		
Scale 2:1	Free size tol.			Ref.		
				Sub.		
Created by ZHUANGJ		Inspected by LUOK	Standardisation HOFFMANN	Date 2018-11-29	State Final Release	
Title D-Sub str SMT 9-pole fem ass with screw nut & pin					Doc-Key / ECM-Nr. 100236647/UGD/001/C 500000139800	
Type TB	Number 0955155X61X				Rev. C	Page 1/1

All Dimensions in mm
Original Size DIN A3
 All rights reserved
 Department EL PD
 HARTING Electronics GmbH
 D-32339 Espelkamp