





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED	04FEB2021	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1




CIRCUIT NO




AS SHOWN :
20POS(X-KEY)1-2040516-0

20	X	9	18.0	22.6	GOLD PLATED	1-2040516-0
18	X	8	16.0	20.6	Sn PLATED	3-2040516-9
18	X	8	16.0	20.6	GOLD PLATED	1-2040516-9
10	X	4	8.0	12.6	Sn PLATED	3-2040516-5
10	X	4	8.0	12.6	GOLD PLATED	1-2040516-5
POS	KEY	n	A	B	FINISHED	PART NO




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 22JUL2008	TE Connectivity			
DIMENSIONS: mm		CHK T. KUDO 22JUL2008				
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±5°		APVD S. MANABE 22JUL2008	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 4-20POS			
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±		PRODUCT SPEC 108-78268	SIZE A300779			
MATERIAL 1		APPLICATION SPEC 114-5377	CAGE CODE C-2040516			
FINISH 2 3 4		WEIGHT -	DRAWING NO C-2040516			
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 3		REV B2

P	LTR	DESCRIPTION	DATE	DWN	APVD



CAVITY MARK


KEYING MARK



CIRCUIT NO

SERIES CODE

LOGO MARK



10POS(X-KEY): 1-2040516-5

①. 材料：ハウジング：ガラス入り熱可塑性ポリエステル樹脂（94V-0）、色：黒
コンタクト：銅合金
リテンションレグ：錫めっき済銅合金

②. めっき（全面）：ニッケル下地めっき1.27μm以上

③. めっき（接触部）：②の上に金めっき0.38μm以上，またはsn1.0 μm以上

④. めっき（コンタクト半田付部）：②の上に錫めっき2μm以上

5. 文字の形状、大きさ、および位置については、大略を示すものであり、
詳細を示すものではありません。

①. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY


②. FINISH(ALL OVER): NICKEL PLATING 1.27μmMIN

③. FINISH(CONTACT AREA): GOLD PLATING 0.38μmMIN OR
Sn PLATING 1.0μmMIN AFTER ②

④. FINISH(CONTACT TAIL): TIN PLATING 2μmMIN AFTER ②
5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT:		DWN	SEE SHEET 1	 TE Connectivity	
DIMENSIONS:		CHK	SEE SHEET 1		
		APVD	SEE SHEET 1	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 4-20POS	
		PRODUCT SPEC	SEE SHEET 1		
		APPLICATION SPEC	SEE SHEET 1	SIZE A300779	
		WEIGHT	-		
MATERIAL		FINISH	-	DRAWING NO C-2040516	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING		RESTRICTED TO	
0 PLC	±	SCALE		SHEET	
1 PLC	±	4:1		2 OF 3	
2 PLC	±				
3 PLC	±				
4 PLC	±				
ANGLES	±				
				REV	
				B2	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			




ROW ID
BOTH SIDE

CIRCUIT NO


CAVITY MARK
ALPHABET:CAPITAL LETTER

KEYING MARK



SERIES CODE


LOGO MARK



HSG

CONTACT

RETENTION LEG



18POS(X-KEY) : 1-2040516-9

THIS DRAWING IS A CONTROLLED DOCUMENT:		DWN	SEE SHEET 1	 TE Connectivity	
DIMENSIONS:		CHK	SEE SHEET 1		
		APVD	SEE SHEET 1	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 4-20POS	
		PRODUCT SPEC	SEE SHEET 1		
MATERIAL		APPLICATION SPEC	SEE SHEET 1	SIZE	CAGE CODE
		WEIGHT	-	A3	00779
FINISH		CUSTOMER DRAWING		DRAWING NO	RESTRICTED TO
				C-2040516	
				SCALE	SHEET
				4:1	3 OF 3
				REV B2	