



FT3B4/0, Power Distribution Block

By Burndy
Catalog # FT3B4/0



Power Distribution Block, Max. 2 Wires per Phase, 3/0-4/0 AWG (Run), 6-4/0 AWG (Tap).

General

Catalog Number	FT3B4/0
Connector Type	Power Distribution Block
Hex Size	1/4
Installation Torque	200 LBS/in
Recommended in-lb	
Material	Aluminum
Number Of Poles	3
Temperature Rating	194
Trade Name	U-BLOK™
UPC	781810113721
UPC 12 Digit	7818101137211

Dimensions

Dimension - Height fraction	4-1/8
Dimension - Height inch	4.13 in
Dimension - Height mm	105 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - Width fraction	3-7/8 in
Dimension - Width inch	3.88 in
Dimension - Width mm	99 mm
Weight	1.25 lb

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0-4/0 AWG

Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	6-4/0 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	3/0-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	6-4/0 AWG
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- Catalogs - [BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- Customer Notices - [Prop 65 Notice](#)
- Interactive Catalog - [BURNDY Full-Line Digital Catalog](#)
- Product Cross Section Image(s) - [BUR_u-blok_la](#)
- Sales Drawings - [sd210528-01](#)
- Specifications - [BURNDY_FT3B40_Specsheet](#)
- Specifications - [FT3B4/0](#)

