


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Receptacle
? Tab Fit = 6.35 x 0.81 mm
? Wire Range = 1.00 -2.50 ² [17-13.5]
mm [AWG]
? Insulation Diameter = 3.00 -4.29
[.118 -.169] mm [in]
? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

? [TERMINAL, 6,3 SERIES FATIN FATON RCPT.](#) (PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

Product Type Features:

? Product Type = Receptacle

? Tab Fit (mm [in]) = 6.35 x 0.81 [.250 x .032]

? Insulation Diameter (mm [in]) = 3.00 -4.29
[.118 -.169]

? Receptacle Style = Straight

? Wire/Cable Type = Regular Wire

? Finish = None

? Material = Brass

? Insertion Force = Normal

? Insulation Support = With

? Crimp Type = "F"

? FASTON = Yes

? Wire Range (mm [AWG]) = 1.00 - 2.50 ² [17-13.5]

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Packaging Method = Strip

```
? Line = FASTIN -FASTON .250
? Brand = AMP
```