



Part Number : [1301050038](#)

Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer 117V - 12V, with Steel Screw Release Guard, Cord Type 14/2 SOOW, NEMA 5-15 Plug, 15.24m (50.0') Cord Length

Series Number : 130105

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1621-12B



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer 117V - 12V, with Steel Screw Release Guard, Cord Type 14/2 SOOW, NEMA 5-15 Plug, 15.24m (50.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862529

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	15.24m (50.0')
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW

Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 22, 2025