



Part Number : [351500300](#)

Product Description : VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural

Series Number : 35150

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[351500300_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)


[351500000AS_KOR-000.pdf](#)

[PK-35150-003-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Connector Housings |
| Series | 35150 |
| Description | VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural |
| Application | Power, Wire-to-Wire |
| Product Name | VersaBlade |
| UPC | 800753183643 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Physical

| | |
|-----------------------|------------|
| Circuits (maximum) | 3 |
| Color - Resin | Natural |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |

| | |
|-------------------------------|----------------|
| Material - Resin | PBT |
| Net Weight | 3.335/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 7.30mm |
| Pitch - Termination Interface | 7.30mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +120°C |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---------------------------------|-----------------------|
| VersaBlade Hybrid Plug Housings | 35151 |

Use with Part(s)

| Description | Part Number |
|--|----------------------------|
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural | 351500390 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red | 351500392 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow | 351500393 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue | 351500394 |
| VersaBlade Male Crimp Terminal, 24-22 AWG, Type C | 2270288400 |
| VersaBlade Female Crimp Terminal, 24-22 AWG, Type C | 2270298400 |
| VersaBlade Male Crimp Terminals | 35745 |
| VersaBlade Female Crimp | 35746 |

| | |
|---------------------------------|--------------|
| Terminals | |
| VersaBlade Male Crimp Terminals | <u>35747</u> |

This document was generated on Apr 15, 2026