

1

2

3


4

5


6

7

A




B




C

D



CENTRONIC P.C.B. RIGHT ANGLE FEMALE WITH
SPRING LATCH SCREW LOCK GROUND HOOK



P.C.B. LAYOUT

Product Specification

Material

Insulator :Glass-Filled Thermoplastic PBT,UL94V-0 rated,Blue

Contact :Brass

Shell :Steel, 100u" Tin Over 50u" min Nickel.

Boardlock :Brass, 100u" min Nickel Plated.

Electrical

Contact Resistance :20 milliohms Max at 3 AMP DC.

Insulation Resistance :1000 magohms at 500 VDC

Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute

Current Rating :5 AMP

Volatge Rating :250 VAC/rms 60Hz

Dimensions

Positions	C	A	F	D
14	12.96	25.6	36.0	43.9
24	23.76	36.3	46.8	54.7
36	36.72	49.3	59.6	67.7
50	51.84	64.4	74.9	82.8

E

E

F

F

G

G

H

H

RoHS compliant

Unit:mm

Scale	Free						Date	Name	Customer-No.
TOLERANCE									
X.	±0.38					Drawn	30.06.1999	Hellwig	
X.X	±0.25	④	Update	19.08.2015	Winnie	Approved	19.08.2015	Winnie	ASSMANN WSW-No. A-57/xx FR/KL
X.XX	±0.13	③	Update	19.04.2013	Winnie				
X.°	±3°	②	Update	30.06.2009	Dean	ASSMANN WSW components			
X.X°	±1.0°	①	Drawn	30.06.1999	Hellwig				
		Id.	Modification	Date	Name				
									Drawing-No. ASS 0361 CO Replace
									rev04 Sheet

1

2

3

4

5

6

7

SVxxx