
Data sheet

# H1,5/14 R

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

## General ordering data

| | |
|---|---|
| Version | Wire-end ferrule, Standard, 10 mm, 8 mm, red |
| Order No. | 0463100000 |
| Type | H1,5/14 R |
| GTIN (EAN) | 4008190065089 |
| Qty. | 500 items |
| Packaging | loose |



Downloaded from Arrow.com.

# Data sheet

## H1,5/14 R

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals |  |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

### Dimensions and weights

| | |
|---|---|
| Net weight | 0.11 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Technical data

| | | | |
|---|---|---|---|
| Description of article | Wire end ferrule with plastic collar, red | Version | Standard |

### Wire-end ferrules

| | | | |
|---|---|---|---|
| Contact surface diameter (D1) | 1.7 mm | Contact surface length (L2) | 8 mm |
| Collar diameter (D2) | 3.5 mm | Plastic collar thickness (S2) | 0.25 mm |
| L1 in mm | 14.00 mm | Wire connection cross section AWG, max. | AWG 16 |
| Metal sleeve thickness (S1) | 0.15 mm | Stripping length | 10 mm |
| Conductor cross-section | 1.5 mm² | Colour code | Weidmueller |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |




Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Drawing






Downloaded from Arrow.com.