


TOP LEVEL NUMBER	US NUMBER	CHINA NUMBER	TYPE	DM X (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9501-205	98-0003-3115-1	59-0000-0204-4	FFC	8.00" [203.20]	AG500	23655
17-9501-226	98-0003-3117-7	59-0000-0205-1	USB R	8.00" [203.20]	AG500	23655
17-9501-227	98-0003-3118-5	59-0000-0206-9	SER	8.00" [203.20]	AG500	23655
17-9501-206	98-0003-3116-9	N/A	NOV	SEE DWG	AG500	23655



1. WEIGHT OF GLASS IN GRAMS: $1727 \pm 10\%$
2. NICOMATIC HOUSING P/N: OLOS
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

UNITS	INCHES [MM]
TOLERANCES (UNLESS OTHERWISE SPECIFIED)	.X .XX .XXX ANGLES $\pm 1^\circ$
FINISH AND PROTECTION	± .03 [.76] ± .015 [.38] © COPYRIGHT 2004 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY. NO PART OF THIS DOCUMENT MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT 3M WRITTEN PERMISSION OR USED FOR DISSEMINATION OF OTHER THAN 3M AUTHORIZED PURPOSES.  3M TOUCH SYSTEMS MENFEN, MA USA

D	REVISE PER CO 034264	2/12	SB
C	REVISE PER CO 033640	10/11	SB
02	REVISE PER CO 030452	6/09	SB
REV	CHANGE NOTICE	DATE	DRW

MARKETING DRAWING
SCT32NN 26.52" W

 DO NOT SCALE DRAWING	DATE	1 = 1	SIZE C	DOCUMENT NO. 35704-MKT	REV D
	DATE	1 = 1			