
Part Number : 191180056
Product Description : Krimptite Flanged Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
Series Number : 19118
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : BB-116-08



Documents and Resources

Drawings

191180056_sd.pdf

PK-19902-001-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19118
Description	Krimptite Flanged Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
Keyword	Spade Terminal, Spade Terminals
Product Name	Krimptite
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800755082630

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	up to 35kV

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper

Downloaded from Arrow.com.

Material - Plating Mating	Tin
Net Weight	0.564/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	8 (M4)
Temperature Range - Operating	-50° to +149°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm^2	1.00-2.50

Application Tooling

Downloaded from Arrow.com.