


UNIT:MM

REVISION INFORMATION

Rev.	Rev. Date	Modified By	Brief Description
A/1	20-02-27	B0225C01	Changing Drawing



PIN ASSIGNMENT:


P1		P2
1	RED	1
2	WHITE	2
3	GREEN	3
4+5	BLACK	4
SHELL DRAIN+BRAID		SHELL

Electrical test:

1. 100% short, open, miswire test
2. Conduct resistance: 20Ω (max)
3. Insulation resistance: 10MΩ (min)
4. dielectric test: DC 300V

CABLE WHITE PRINT

E166160 AWM 2725 80°C 30V
28AWGX1P+28AWGX2C USB2.0



1PCS/PE BAG

PART NO	WIRE LENGTH "L"	BUYER COLOR	VENDOR COLOR	CUT LENGTH
102-1072-BL-00100	1000 ± 30		BLACK	985-990MM

⑧	TIE	1	BLACK L=120mm
⑦	PE BAG	1/10	CLEAR SIZE: 280X330X0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130X230X0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
⑤	OUT JACKET	6g	BLACK PVC-55P (MOULD NO: 2002-527)
④	OUT JACKET	6g	BLACK PVC-55P (MOULD NO: WM-173)
③	CABLE	1	USB2.0 UL2725 [28AWGX1P+28AWGX2C]+AEB JACKET: BLACK OD: 3.8mm (671-线规-E-1)
②	CONN	1set	USB A MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	1	MICRO USB 5P A/M SOLDER TYPE SHELL: NICKEL PIN: G/F INSULATOR COLOR: BLACK
NO.	NAME	QTY	SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY:	DATE: 2020/02/27	DESCRIPTION: 4C CABLE USB A/M+MICRO USB
CHECKED BY:	SHEET 1 of 1	ITEM NO. As above
APPROVED BY:	SCALE 1:1	REV. A/1 UNIT: mm