

Part Number : [1301030052](#)

Product Description : Watertite Wet Location
Incandescent Hand Lamp, 100W with Screw Release
Grounded Insulated Reflector Guard, Cord Type 16/3
SOOW, 15.24m (50.0') Cord Length

Series Number : 130103

Status : Obsolete

Product Category : Lamps and Lights

Engineering Number : 1203RIB163



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Insulated Reflector Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861359

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Grounded, Insulated, Reflector, Screw Release

Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 13, 2025

Obsolete