


1		2		3		4	
CUSTOMER P/N	FCI P/N	L/mm	L1/mm				
08-0204-01-01	10125715-P0013YYLF	127±4	20REF				

A

B

C

D




NOTES:

1.TEST:

□/S:100% TEST.
 CONNECTION RESISTANCE: 2 Ωhm MAX.
 HI-POT:300V/10mS.
 INSULATION RESISTANCE: 10M Ωhm MIN.

2. PART NUMBER SCHEME FOR CABLE ASSEMBLY:


10125715 -P XXXX Y Y LF






3. ROHS COMPLIANCE

4. LABEL CONTENT:

08-0204-01-01-----CUSTOMER P/N
 FCI WYYY-----DATE CODE (WEEK & YEAR)
 CHINA



No.	DESCRIPTION	QTY	UNIT
③	Lable	1	EA
②	Minitex 2x4 position IDC receptacle, 0.2um gold, with central key and friction latch bump	2	PC
①	Flat cable UL21682, 28AWG*8C, Pitch1.0,Halogen Free Polyolefin 3M P/NHF625/08	A/R	M

www.fciconnect.com			surface - - ✓ -		tolerance std - -		projection 		mm 					
			TOLERANCES UNLESS		OTHERWISE SPECIFIED									
Dr	Harry Shi	2013-07-03	ANGULAR	LINEAR	0.X	±-	size	A3	Scale					
Eng	Harry Shi	2013-07-03			0.XX	±-			n/a					
Chr	Harry Shi	2013-07-03			0°	±'	0.XXX	±-	ECN					
Appr	Jackson Wang	2013-07-03	Product family					Spec ref		-				
			title			Minitex IDC Cable Ass'y			dwg no		10125715		Rev. A	
			catalog no			-			CUSTOMER		sheet 1 of 1			

rev	ecn no	dr	date
A	-	SHH	2013-07-03
G	-	-	-

REV F - 2006-04-17