

2943592

<https://www.phoenixcontact.com/us/products/2943592>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Complete housing, with vents, width: 50 mm, height: 102 mm, depth: 115.5 mm, color: black (similar RAL 9005), cross connection: Not provided for

Your advantages

- Robust housing technology
- Easy snap-on mounting on symmetrical DIN rails in accordance with EN 60715
- Touch-proof and contamination-proof accommodation of the electronics
- Flexible accommodation of different connection elements (from high-position connectors to electronic PCB terminal blocks)

Commercial data

Item number	2943592
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCDA
GTIN	4017918081195
Weight per piece (including packing)	146.42 g
Weight per piece (excluding packing)	146.42 g
Customs tariff number	84879090
Country of origin	DE

CM 50-LG/H 12,5/BO BK - Electronics housing



2943592


<https://www.phoenixcontact.com/us/products/2943592>

Technical data

Product properties

Product type	Complete housing
Housing type	DIN rail housing
Housing series	CM
Product family	CM LG
Type	Housing closed, ventilation slots

Dimensions

Dimensional drawing	
Width	50 mm
Height	102 mm
Depth	115.5 mm

Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	V0
Housing material	Polycarbonate, glass-fiber-reinforced
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

CM 50-LG/H 12,5/BO BK - Electronics housing


2943592

<https://www.phoenixcontact.com/us/products/2943592>




Drawings

Dimensional drawing



Dimension A: 115.5 mm; dimension B: 102 mm; dimension C: 50 mm

Dimensional drawing



PCB 1, 7: Dimension A: 47.5 mm; B: 102.0 mm; C: 6.5 mm

PCB 8, 13: Dimension A: 100.0 mm; B: 102.0 mm; C: 6.5 mm

PCB 10: Dimension A: 100.0 mm; B: 92.3 mm; C: 0 mm


CM 50-LG/H 12,5/BO BK - Electronics housing

2943592

<https://www.phoenixcontact.com/us/products/2943592>



Schematic diagram



CM 50-LG/H 12,5/BO BK - Electronics housing

2943592

<https://www.phoenixcontact.com/us/products/2943592>



Classifications

ECLASS

ECLASS-13.0	27190101
ECLASS-15.0	27190101

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

CM 50-LG/H 12,5/BO BK - Electronics housing



2943592

<https://www.phoenixcontact.com/us/products/2943592>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com