Product Line

- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
  - M20
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub







LC20-03BFMA-SL8001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Metal, Shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search


Heavy Duty Shielded,...
− 0 +


Heavy Duty Shielded,...
− 0 +


Heavy Duty Shielded,...
− 0 +


Heavy Duty Shielded,...
− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **20A**	Connector Type **Field Installable**
Shielded **Metal, Shielded**	No. of Contacts **03**
Connector Gender **Female**	Backshell **Straight**
Mating Style **Screw Thread**	IP Rating **IPX8**
Assembly Style **Solder**	

More Options

People Also Bought

Downloaded from Arrow.com.