
Part Number : 2051950360
Product Description : Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Plug, 70.00mm Shielded FFC, Vertical, 7.10mm Mated Height, 36 Circuits
Series Number : 205195
Status : Obsolete
Product Category : FFC / FPC Connectors



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Obsolete

Downloaded from Arrow.com.

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	FV2R
Description	Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Plug, 70.00mm Shielded FFC, Vertical, 7.10mm Mated Height, 36 Circuits
Contact Type	Dual
Product Name	Easy-On
UPC	191128792943

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Flexi-Latch
Circuits (Loaded)	36
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	20
Mated Height	7.10mm
Material - Resin	Polyester
Net Weight	1384.400/mg
Orientation	Vertical
Packaging Type	Bag
PCB Mounting	N/A
PCB Retention	N/A
Pitch - Mating Interface	0.50mm
Polarized to PCB	N/A
Stackable	No
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Receptacle, Vertical, Dual Contact, 3.90mm Height, 7.10mm Mated Height, Gold (Au) Plating, 36 Circuits	2051960360

This document was generated on Sep 07, 2026

Obsolete

Downloaded from Arrow.com.